

Tz265 Extra data

Tank 1 Sodium Hydroxide

Front agitated..... rear heated

Tank 2 Sodium Hydroxide Texture etch

Front agitated.....Rear Heated and condenser coil

Tank 3 Sodium Hydroxide Grove Etch

Front Agitated.....Rear Heated

Tank 4 Hydroflouric Dilute HF acid

Tank 5 Dilute Hydrochloric acid

Front Agitated

Tank 6 Static rinse Di water

2 off Serfilco pumps model no:45-0027 MA

5 off air diaphragm pumps 1 for each tank

12 off air operated valves

3 off omron c5ck temp controllers

1 off thornton 200cr conductivity/resistivity instrument